



QPX2828

by Burndy
Catalog ID: QPX2828

Prop 65 Notice

Parallel Clamp, Copper: 1-4/0 AWG (Run)/ 1-4/0 AWG (Tap).

Features: The VERSITAP Type QPX Is Recommended For Tee, Cross, Parallel, Butt And Tap Connections, Range-Taking, Only 10 Connectors Required To Accommodate Conductor Sizes From #6 Stranded To 1000 KCMIL, Edges Are Rounded For Easy Taping, Made Of High Strength, High Conductivity Copper Alloy And Silicone Bronze DURIUM Hardware, Conductor Type: Run And Tap: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Stud/bolt Size: 3/8 IN, Length: 1-7/8 IN, Installation Torque: 250 IN-LB, Width: 1-7/8 IN, Height: 2-1/8 IN

Product Details

General

Application	For Tee, Cross, Parallel, Butt And Tap Connections, Copper, Copperweld And Copperweld-Copper
Installation Torque Recommended in-lb	240 LBS/in
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Trade Name	VERSITAP™
Type	QPX
UPC	781810342503

Dimensions

Dimension - Height fraction	2-3/8
Dimension - Height inch	2.38 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Width fraction	1-13/16 in
Dimension - Width inch	1.81 in
Dimension - Width mm	46 mm

Conductor Related

Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1 AWG-4/0 AWG
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1 AWG-4/0 AWG
Conductor - CopperWeld Solid Run	9 AWG;8 AWG;7 AWG;6 AWG;5 AWG
Conductor - CopperWeld Solid Run Range	9 AWG-5 AWG
Conductor - CopperWeld Solid Tap	9 AWG;8 AWG;7 AWG;6 AWG;5 AWG

Conductor - CopperWeld Solid Tap Range	9 AWG-5 AWG
Conductor - CopperWeld Str Run	3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG;1 F AWG;1 G AWG;1 J AWG;1 K AWG;1 N AWG;1/0 F AWG;1/0 G AWG;1/0 J AWG;1/0 K AWG;2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG;3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - CopperWeld Str Run Range	3 A AWG-3/0 V AWG
Conductor - CopperWeld Str Tap	3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG;1 F AWG;1 G AWG;1 J AWG;1 K AWG;1 N AWG;1/0 F AWG;1/0 G AWG;1/0 J AWG;1/0 K AWG;2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG;3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - CopperWeld Str Tap Range	3 A AWG-3/0 V AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU Weld C Str-Run • CU Weld C Solid-Run • CU C Str-Tap • CU Weld C Str-Tap • CU Weld C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)