



## QPX282CY

by Burndy  
Catalog ID: QPX282CY

Prop 65 Notice

Universal Parallel Clamp For Copper and Aluminum, 5/16 in L, 1-1/2 in, 1/0 Str. - 4/0 Str. (Run), 6 Str. - 2 Str.

Features: High Copper Alloy Cast Connector, Tin-Plated For Use With Copper Or Aluminum Cable, Makes Parallel, Tap, Tee, Cross Or End-To-End Connections, Edges Rounded For Easy Taping, PENETROX Joint Compound Recommended, Number Of Bolts: 2, Installation Torque: 150 IN-LB, Conductor Type: Run: Commercial Stranded Aluminum, Commercial Stranded Copper, Tap: Commercial Stranded Aluminum, Commercial Stranded Copper, Width: 1-7/8 IN, Height: 1-7/8 IN, Length: 1-1/2 IN

## Product Details

### General

Application	For Use With Copper Or Aluminum Cable
Installation Torque Recommended in-lb	150 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX-Y, Universal
UPC	781810342107
UPC 12 Digit	7818103421077

### Dimensions

Dimension - Height fraction	1-7/8 in
Dimension - Height inch	1.88
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.84
Dimension - Width mm	47 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
------------------------	---------------------------------

Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1/0 -4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)