



QPX4434Y

by Burndy
Catalog ID: QPX4434Y

Prop 65 Notice

VERSITAP

Product Details

General

Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810345405
UPC 12 Digit	7818103454055

Dimensions

Dimension - Height fraction	3-1/3 in
Dimension - Height inch	3.19
Dimension - Width inch	2.91
Dimension - Width mm	74 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Run Range	750 kcmil-1000 kcmil
Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Tap Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)