

QQA262

by Burndy
Catalog ID: QQA262



Copper Terminal, Heavy Duty, 2 Hole, 1/0-2/0 AWG (Str), 3/8" Stud, 1" Stud Hole Spacing, 2 Screws.

Features: Type QQA Heavy Duty, High Copper Alloy Terminal For Joining Cable To Equipment Pads Or Bar, Twin Clamping Elements Secure Joint Vibration And Flexing, One-Wrench Installation, Dimension K: 13/32 IN, Dimension N: 7/16 IN, Dimension T: 7/32 IN, Number Of Clamping Elements: 2, Dimension D: 1-15/16 IN, Conductor Type: Run: Commercial Stranded Copper, Navy Copper, Tongue Width: 13/16 IN, Installation Torque: 180 IN-LB, Height: 1-3/16 IN, Length: 4-3/16 IN

Product Details

General

Application	For Joining Copper Cable To Equipment Pads Or Bars
Connector Type	Terminal
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR, QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325858

Dimensions

Dimension - D inch	1.94 in
Dimension - F Width Center to Center inch	1.00 in
Dimension - Height fraction	1.125 in
Dimension - Height inch	1.13 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.19 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.81 in

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy;125 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)