

QQA28

by Burndy
Catalog ID: QQA28

Prop 65 Notice

Copper Terminal, Heavy Duty, 1 Hole, 3/0-4/0 AWG (Str), 3/8" Stud, 2 Screws



Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	250 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325759

Dimensions

Dimension - D inch	1.06 in
Dimension - Height fraction	1.3125 in
Dimension - Height inch	0.406
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	10.31
Dimension - L Length Overall mm	90 mm
Dimension - Length Overall inch	3.56 in
Dimension - N inch	0.53 in
Dimension - Pad Width inch	1.00 in

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy;200 (61) Navy
Conductor - Copper Str Navy Size Range	150 (61) Navy-200 (61) Navy
Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)