

QQA312N

by Burndy
Catalog ID: QQA312N

Prop 65 Notice

Copper Terminal, Heavy Duty, 2 Hole, 250-350 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

Features: Type QQA Heavy Duty, High Copper Alloy Terminal For Joining Cable To Equipment Pads Or Bar, Twin Clamping Elements Secure Joint Vibration And Flexing, One-Wrench Installation



Product Details

General

Application	For Copper Cable
Connector Type	Terminal
Installation Torque Recommended in-lb	325 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810326008

Dimensions

Dimension - D inch	3.13 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1.6896551724137931 in
Dimension - Height inch	1.69 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.19 in

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy;300 (91) Navy;350 (91) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy
Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)