

## QQA342N

by Burndy  
Catalog ID: QQA342N

Prop 65 Notice

Copper Terminal, Heavy Duty, 2 Hole, 400-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

Features: Type QQA Heavy Duty, High Copper Alloy Terminal For Joining Cable To Equipment Pads Or Bar, Twin Clamping Elements Secure Joint Vibration And Flexing, One-Wrench Installation



## Product Details

### General

Application	For Copper Cable
Connector Type	Terminal
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810326107

### Dimensions

Dimension - D inch	3.13 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	162 mm
Dimension - Length Overall inch	6.38 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.38 in

### Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy;500 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil

Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Str Navy-Size</li></ul>
----------------	--

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)