



QR26

by Burndy
Catalog ID: QR26

Prop 65 Notice

Splice or Reducer Qiklink, 1/0 Str. - 2/0 Str., 2-1/8 in L, 13/16 in W.

Features: High Copper Alloy Splicer/Reducer For Joining A Range Of Cable End To End, Neat, Compact Easy To Tape Installation, One-Wrench Installation, Conductor Type: Copper, Installation Torque: 180 IN-LB

Product Details

General

Application	For Joining A Range Of Copper Cable End To End
Connector Type	Splice;Reducer
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper Alloy
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLINK
Trade Name	QIKLINK™
Type	QR
UPC	781810334423

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Height fraction	1-1/4 in
Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.13 in
Dimension - Width fraction	13/16 in
Dimension - Width inch	0.81 in
Dimension - Width mm	21 mm

Conductor Related

Conductor - Copper Solid Size A	1/0 AWG;2/0 AWG
Conductor - Copper Solid Size A Range	1/0 AWG-2/0 AWG
Conductor - Copper Solid Size B	1/0 AWG;2/0 AWG
Conductor - Copper Solid Size B Range	1/0 AWG-2/0 AWG
Conductor - Copper Str Size A	1/0 ;2/0 AWG
Conductor - Copper Str Size A Range	1/0 -2/0 AWG

Conductor - Copper Str Size B	1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	1/0 -2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)