



## QR40

by Burndy  
Catalog ID: QR40

Prop 65 Notice

Splice or Reducer, 600 - 800 kcmil, Recommended Tightening Torque:  
500 IN-LB

## Product Details

### General

Connector Type	Splice;Reducer
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper Alloy
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLINK™
UPC	781810334782

### Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.63 in
Dimension - Height fraction	2-1/2 in
Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

### Conductor Related

Conductor - Copper Str Size A	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size A Range	600 kcmil-800 kcmil
Conductor - Copper Str Size B	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size B Range	600 kcmil-800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• CU C Str-Size B</li> <li>• CU C Solid-Size A</li> <li>• CU C Solid-Size B</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	2
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)