

RK142ABOX100

by Burndy
Catalog ID: RK142ABOX100

Closed Insulated end Splice



Product Details

General

Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	N
Plating Type	Unplated
UPC	781810029473
UPC 12 Digit	7818100294733

Dimensions

Dimension - B Length fraction	11/25 in
Dimension - B Length inch	0.44 in
Dimension - Length Overall inch	0.72 in
Dimension - Pad Width inch	0.38 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG;17 AWG;16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	20 -14 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)