



RYA29UCR

by Burndy
Catalog ID: RYA29UCR

Prop 65 Notice

URD MOLE Tap Assembly (Force Fit Sleeve), 250 kcmil Cu, 250 kcmil Comp, 250 kcmil Al

Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	299;655;705
Insulation	Y
Insulation Type	Rubber
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Trade Name	MOLE™
UPC	781810182000

Dimensions

Dimension - B Length inch	2 in
Dimension - D inch	1.11 in
Dimension - Length Overall inch	3.15 in
Dimension - Pad Width inch	1.11 in
Dimension - Strip Length inch	2-1/16

Conductor Related

Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)