



## RYA2WACR

by Burndy  
Catalog ID: RYA2WACR

BURNDY; MOLE; RYA-ACR; The Kits Consists of Universal Hylug, Mounting Hardware and Pre-lubricated Forcefit Rubber Sleeve, Installed With Common Installation Tools, Three Die Sets Install a Range of 4 STR-350 MCM, The Rubber Sleeve has Internal Sealing Rings that Provide a Positive Moisture Seal by Exerting Circumferential Force on Cable and Mole Insulation; For Aluminum or Copper With Type RDM-28 URD MOLE; RoHS Under Investigation; Conductor Range: 2 SOL EC-O Aluminum

## Product Details

### General

Connector Type	Terminal
Die Index	BG
Insulation	Y
Insulation Type	Rubber
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
UPC	781810311332

### Dimensions

Dimension - B Length inch	1.42 in
Dimension - D inch	0.65 in
Dimension - Length Overall inch	2.5 in
Dimension - Pad Width inch	0.65 in
Dimension - Strip Length inch	1-1/2

### Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

### Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)

