

S2GBP44A

by Burndy
Catalog ID: S2GBP44A

Prop 65 Notice

Two Conductor 18 IN Spacer, 795 kcmil-874 kcmil ACSR, 954 kcmil AAC



Product Details

General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lbs-in
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810142035
UPC 12 Digit	7818101420355

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.165 in
Dimension - Diameter Min Size inch	1.092 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	550 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size	795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil
Conductor - ACSR Str Size Range	795 (54/7) Condor kcmil-874.5 (54/7) Crane kcmil
Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)