

# S2GBP46A8

by Burndy  
Catalog ID: S2GBP46A8

Prop 65 Notice

Two Conductor 8 IN Spacer, 1272 kcmil(54/19)-1431(54/19) kcmil ACSR, 1590 kcmil-1600 kcmil AAC, 550kV



## Product Details

### General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lbs-in
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810285565
UPC 12 Digit	7818102855655

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.504 in
Dimension - Diameter Min Size inch	1.382 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Electrical Ratings

Rating - KVA	550 kV
--------------	--------

### Conductor Related

Conductor - ACSR Str Size	1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil;1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1272 (54/19) Pheasant kcmil-1431 (54/19) Plover kcmil
Conductor - AL Str Size	1590 kcmil;1600 kcmil
Conductor - AL Str Size Range	1590 kcmil-1600 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)