

## S2R44ACG18

by Burndy  
Catalog ID: S2R44ACG18

Streamlined Spacer Clamp, Accommodates: 1000 KCMIL Copper



### Product Details

#### General

Application	Substation
Connector Type	Spacer
Material	Aluminum Alloy
One Wrench Installation	Y
Plated	N
UPC	621945132757
UPC 12 Digit	6219451327577

#### Dimensions

Dimension - Height inch	1.86 in
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.56 in
Dimension - Width inch	1.86 in
Dimension - Width mm	47 mm

#### Electrical Ratings

Rating - KVA	230 KV
--------------	--------

#### Conductor Related

Conductor - Connection Combination	Cable Spacer
Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str Size Range	1000 KCMIL
Number Of Conductors	2

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)