

S2R47ACG1

by Burndy
Catalog ID: S2R47ACG1

Two Conductor 15 IN Cable Spacer, 1.361 IN-1.545 IN Dia AL Cable, 345kV



Product Details

General

Application	Substation
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque Recommended in-lb	660 LBS/in
Material	Aluminum Alloy
One Wrench Installation	Y
Plating Type	Unplated
UPC	621945113671
UPC 12 Digit	6219451136711

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.12 in
Dimension - L Length Overall mm	448 mm
Dimension - Length Overall inch	17.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - AL Str Size Range	1.361 in-1.545 in
Conductor - Connection Combination	Cable Spacer
Conductor Spacing	15 in
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)