

## S2R496A15S7HQ

by Burndy  
Catalog ID: S2R496A15S7HQ

Prop 65 Notice

Rigid 15 IN Spacer, 735kV



## Product Details

### General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	660 in-lb
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810480120
UPC 12 Digit	7818104801200

### Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	2.50 in
Dimension - Diameter Min Size inch	2.28 in
Dimension - Height inch	4.10 in
Dimension - L Length Overall mm	465 mm
Dimension - Length Overall inch	18.30 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Electrical Ratings

Rating - KVA	735 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Cable Spacer
Number Of Conductors	2

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	2
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)