

S2R59RCG1

by Burndy
Catalog ID: S2R59RCG1

Prop 65 Notice

Rigid 13 IN Spacer, 1843.2 kcmil ACSR, 735kV



Product Details

General

Application	Substation
Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque Recommended in-lb	660 in-lb
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	781810460245
UPC 12 Digit	7818104602455

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.76 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	735 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size Range	1843.2 kcmil
Conductor - Connection Combination	Cable Spacer
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)