

S2RA45A844NR90

by Burndy
Catalog ID: S2RA45A844NR90

Rigid Spacer, Accommodates: 1200 KCMIL - 1300 KCMIL ASC, 1033.5 KCMIL - 1113 KCMIL ACSR



Product Details

General

Application	Substation
Connector Type	Spacer
Material	Aluminum Alloy
Plated	N
UPC	621945337435
UPC 12 Digit	6219453374355

Dimensions

Dimension - Height inch	8.44 in
Dimension - L Length Overall mm	276 mm
Dimension - Length Overall inch	8.00 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	138 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil
Conductor - AL Str Size	1200 KCMIL - 1300 KCMIL
Conductor - AL Str Size Range	1200 KCMIL - 1300 KCMIL

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)