



S3GBP45A

by Burndy
Catalog ID: S3GBP45A

Prop 65 Notice

Three Conductor Spacer, 1192 kcmil-1272 kcmil AAC, 1033.5(54/7) kcmil-1192.5(54/19) kcmil ACSR, 550kV

Product Details

General

Application	Substation
Connector Type	Spacer
Installation Torque Recommended in-lb	480 in-lb
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810209820
UPC 12 Digit	7818102098200

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Diameter Max Size inch	1.333 in
Dimension - Diameter Min Size inch	1.246 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - KVA	550 kV
--------------	--------

Conductor Related

Conductor - ACSR Str Size	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew kcmil-1192.5 (54/19) Grackle kcmil
Conductor - AL Str Size	1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil
Conductor - AL Str Size Range	1192 kcmil-1272 kcmil
Conductor Type	<ul style="list-style-type: none"> AL C Str-Size ACSR C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)