



SC4

by Burndy
Catalog ID: SC4

Plastic Split Bolt Cover, Conductor range for equal Run/Tap: 8 str.-4 Sol.

Features: Used Indoors Or Outdoors This Compact, One-Piece Plastic SERVIT Cover, Saves Time And Material, Eliminates Costly Taping Of Split-Bolts, Positive Latch Snaps Easily And Quickly Over Connector, Ideal For Tight Quarters, Self Positioning Plastic Fingers Wrap Around Wires Fully Insulating Joint, UL Listed For 600 Volt Indoor Application, Three Covers Accommodate A Range Of 6 SERVIT Sizes Through 2/0 Stranded

Product Details

General

Application	For Used In Indoors Or Outdoors Applications, KS17
Sub Brand	SERVIT COVER
Temperature Rating	194
Trade Name	SERVIT®
Type	SC
UPC	781810042502

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)