



SN10B

by Burndy
Catalog ID: SN10B

Cu Butt Splice, Butted Seam Nylon Straight, Smooth Funnel Entry, 10-12 AWG, 600 V, 1.64" L, Nylon Insul, Tin Plated, Yellow(Insul Color).

Features: Manufactured From One-Piece Tin-Plated Seamless Copper Tubing With An Integral Barrel/Insulation Grip: Provides Maximum Tensile Strength, Plus Excellent Cable Support And Strain Relief And Eliminates Failures Due To Vibration, Smooth Funnel Entry: Provides Easy Wire Insertion, Window Position Locator For Full Cycle Ratchet Tool Crimp: Provides Proper Tool/Connector Alignment For Correct Crimp, Nylon Insulation Offers High Dielectric Strength And Stability In Oily Enviromental Conditions: Maintains A High Quality Connection In Demanding Applications, The Nylon Is Locked Into Position: The Connector Will Not Move

Product Details

General

Application	For Heavy Duty Application Requirements
Color Code	Yellow
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	SN
UPC	781810525081
UPC 12 Digit	7818105250811

Dimensions

Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.64 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Strip Length inch	3/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	10 - 12 AWG
-----------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)