



T1010LF

by Burndy
Catalog ID: T1010LF

Copper Compression Terminal, Snap Fork Tongue, 12-10 AWG, #8-#10 Stud, Long Barrel, Tin Plated

Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810530702
UPC 12 Digit	7818105307022

Dimensions

Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z inch	0.29 in

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)