



T1414F

by Burndy
Catalog ID: T1414F

Prop 65 Notice

Uninsulated Copper Compression HYLUG Terminal, Fork Tongue, #20 - 14 AWG, 1/4" stud

Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810722466
UPC 12 Digit	7818107224666

Dimensions

Dimension - L Length Overall mm	23
Dimension - Length Overall inch	0.92 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.39 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)