

T144

by Burndy
Catalog ID: T144

Prop 65 Notice

Uninsulated Compression Terminal, Ring Tongue, 3-4 Stud, .66 in L,
Constructed of pure electrolytic copper



Product Details

General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722329
UPC 12 Digit	7818107223299

Dimensions

Dimension - Hole Size fraction	3/25
Dimension - Hole Size inch	0.12 in
Dimension - L Length Overall mm	17
Dimension - Length Overall inch	0.66 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#3 - #4
Dimension - Z inch	0.28 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)