



## T1610BF

by Burndy  
Catalog ID: T1610BF

Block Fork (Brazead Seam), 22-18 AWG, 8-10, .83 in L, .31 in W

## Product Details

### General

Connector Type	Compression Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Fork Tongue
UPC	781810530825
UPC 12 Digit	7818105308255

### Dimensions

Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.79 in

### Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)