



T166LF

by Burndy
Catalog ID: T166LF

Snap Fork Tongue; 22 AWG -18 AWG; 4-6; .83 in L

Product Details

General

Connector Type	Compression Terminal
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Trade Name	HYLUG™
UPC	781810530832
UPC 12 Digit	7818105308322

Dimensions

Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.32 in

Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)