



TMH268SS

by Burndy
Catalog ID: TMH268SS

Prop 65 Notice

Hardware Kit, Installation Torque: 240 IN-LB, Working Range: 0.44 - 0.69 IN.

Features: Working Range-0.44-0.69 IN, Includes: Bolt (2) 1.25 IN Length, 3/8-16 Thread Size, Flat Washer (4), Split Washer (2), Hex Nut (2), Installation Torque: 240 IN-LB

Product Details

General

Application	A general purpose Fastening Hardware Kit providing long lasting corrosion resistance
Connector Type	Hardware
Installation Torque Recommended in-lb	240 LBS/in
Material	Stainless Steel
Sub Brand	HARDWARE KITS
Type	TMHSS
UPC	781810271414
UPC 12 Digit	7818102714144

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Thread Size	3/8 - 16
Dimension - Threads per inch	16

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)