

TN184F

by Burndy
Catalog ID: TN184F

BURNDY; TN-F, Compression terminal; Voltage Rating: 300 V; Insulation:
Nylon insulated; Material: Copper; Color: Red



Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810530870

Dimensions

Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Pad Width inch	0.23 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	#3;#4
Dimension - Z inch	0.24 in

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)