

TP1010LF

by Burndy
Catalog ID: TP1010LF

Prop 65 Notice

Copper Terminal, Locking Fork Tongue, 12-10 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated.

Features: Type TP-LF Is A Variation Of The Type TP Design And Employs A Locking Fork Tongue For Fast Installation And Security, 600 V Maximum, 105 DEG C Maximum, Locking Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, Internal Configuration Of The Fork: Prevents The Terminal From Coming Off The Screw Without Applying A Pulling Force, Locking Fork Is Made From A Copper Alloy: Permits Many Installations While Maintaining Proper Spring Retention Of Forks, Bulk Catalog Number: BA10EL10, Insulation Diameter (maximum): 0.28 IN, Temperature Rating: 105 DEG C Maximum, Tape Mounted Catalog Number: BA10EL10M, Installation Tool: Ratchet: MR8-89-1, M8ND Tool With N10ET-23 Die, Color Code: Yellow, Wire Strip Length: 19/64 IN, Finish: Electro-Tin Plated, Wire Insulation Grip: No



Product Details

General

Application	For Fast Installation And Security
Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-LF, Locking
UPC	781810713907
UPC 12 Digit	7818107139077

Dimensions

Cable Insulation Diameter Maximum	0.260 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in

Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)