

TP106LF

by Burndy
Catalog ID: TP106LF

Prop 65 Notice

Terminal-Polyvinylchloride Insulated, Locking Fork Tongue, 12-10 AWG,
#4-#6 Stud



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Trade Name	VINYLUG™
UPC	781810713808
UPC 12 Digit	7818107138088

Dimensions

Cable Insulation Diameter Maximum	0.260 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.05 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#6
Dimension - Z inch	0.26 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)