

TP1610Z

by Burndy
Catalog ID: TP1610Z

Prop 65 Notice

Copper Terminal-Polyvinylchloride Insulated, Flanged Fork Tongue, Color Code: Red, #8 -#10 stud, .96 in L, 600 Volts Max., 105 Deg C Max.

Features: VINYLUG Type TP-Z Is A Variation Of The Type TP And Employs A Flanged Fork Tongue For Fast Installation And Security, 600 V Maximum, 105 DEG C Maximum, Flange Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, The Flanges On The End Of The Fork Terminal Aid In Preventing A Slightly Loose Terminal From Becoming Fully Disconnected From The Screw, Flanges Make Re-Securing A Loose Terminal Easier, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1 Tool, Insulation Diameter (maximum): 0.145 IN, Tape Mounted Catalog Number: BA16EZ10M, Bulk Catalog Number: BA16EZ10, Wire Insulation Grip: No, Color Code: Red, Finish: Electro-Tin Plated, Temperature Rating: 105 DEG C Maximum



Product Details

General

Application	For Fast Installation And Security
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810714966
UPC 12 Digit	7818107149666

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	1/4 in

Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)