

TP1810RBG25

by Burndy
Catalog ID: TP1810RBG25

Ring Terminal, 22 - 16 AWG, #2 - #3 Stud, Tin Plated



Product Details

General

Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
Type	Ring Tongue
UPC	781810486559
UPC 12 Digit	7818104865599

Dimensions

Dimension - Stud Size inch	#10
----------------------------	-----

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG
Conductor - Copper Solid Size Range	20 -18 AWG
Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG-18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)