



TTV10

by Burndy
Catalog ID: TTV10

T-Tap Connectors, 10-12 AWG, 0.72" L, 0.38" W, Yellow.

Allows user to tap into a wire in mid-span without cutting or stripping the wire

Product Details

General

Application	for an easy tap off of a run conductor
Color Code	Yellow
Connector Type	T-Tap
Sub Brand	HYDENT
Trade Name	QIKTAP™
Type	Electrical Terminal
UPC	781810525111
UPC 12 Digit	7818105251111

Dimensions

Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.72 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)