

## U2HR153CG3

by Burndy  
Catalog ID: U2HR153CG3

Prop 65 Notice

Copper Bus Connectors, Two 1000 kcmil CU Cable spaced on 6 IN Center



## Product Details

### General

Application	Substation
Connector Type	Bus Support
Fitting Type	Rigid Conduit
Hardware Type	Cap mounting kit (w/o nuts)
Material	Copper Alloy, Cast
Material - Hardware	Galvanized Steel
Mounting Hardware	1/2-13 x 1" GS
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810432396
UPC 12 Digit	7818104323966

### Dimensions

Bolt Circle Diameter	3.00 in
Dimension - G inch	2.06 in
Dimension - Height inch	3.38 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - Width inch	8.75 in
Dimension - Width mm	222 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

## Conductor Related

Conductor - Connection Combination	Base to Cable
Conductor - Copper Str Size	1000 kmcil
Conductor - Copper Str Size Range	1000 kcmil
Conductor Spacing	6 in
Number Of Conductors	2

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)