

U2HR173

by Burndy
Catalog ID: U2HR173

Prop 65 Notice

Copper Bus Connectors, 750kcmil CU - 1 1/2" IPS CU



Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Rigid Conduit
Hardware Type	Cap mounting kit (w/o nuts)
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
Mounting Hardware	1/2-13 x 1" GS
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810095096
UPC 12 Digit	7818100950966

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - B Length inch	4.31 in
Dimension - G inch	2.50 in
Dimension - Height inch	4.42 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.32 in
Dimension - Width inch	6.75 in
Dimension - Width mm	171 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Tube Std Size	1 1/2 IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor Spacing	2.82 in
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)