



UC2834

by Burndy
Catalog ID: UC2834

Prop 65 Notice

CU Parallel Groove Clamp accommodates large number of CU Conductors, Conductor: 4/0 Str. - 500 (Either Groove).

Features: Type UC Connector Accommodates Large Range Of Conductors In Either Groove, Reducing Inventory To A Minimum, Interlocking Finger Design Provides Firm Grip With Maximum Contact Length, High Strength, Corrosion Resistant Silicone Bronze Hardware, One Wrench Installation, Width: 2-1/2 IN, Length: 4-1/4 IN, Height: 2-7/8 IN

Product Details

General

Application	For Range Of Copper
Installation Torque Recommended in-lb	480 LBS/in
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Type	UC
UPC	781810012901

Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - Height fraction	2-3/4 in
Dimension - Height inch	2.75 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)