



UC33R

by Burndy
Catalog ID: UC33R

Prop 65 Notice

Cast Aluminum Alloy TAPIT™, GROOVE A, AL/CU: 4/0 STR - 400 kcmil,
ACSR : 3/0 - 336.4 GROOVE B, AL/CU: 6 SOL - 2/0 STR ACSR : 6 - 2/0
W/INHIBITOR

Product Details

General

Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810097250
UPC 12 Digit	7818100972500

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Height fraction	2-3/4 in
Dimension - Height inch	2.77 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.21 in
Dimension - Width mm	56 mm

Conductor Related

Conductor - AL Str Size A	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Size A Range	4/0 AWG-400 kcmil
Conductor - AL Str Size B	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size B Range	6 AWG-2/0 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Str Size A	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Size A Range	4/0 AWG-400 kcmil
Conductor - Copper Str Size B	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	6 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)