



UCG25RSCONKIT

by Burndy
Catalog ID: UCG25RSCONKIT

Prop 65 Notice

CONTAINS UCG25RS AND COVER GROOVE A Al/Cu: 8Str-1/0Str ACSR:
6-1/0 GROOVE B Al/Cu: 8Str-1/0Str ACSR: 6-1/0 INCLUDES OXIDE
INHIBITOR

Product Details

General

Application	Substation
Connector Type	Split Bolt
Plated	N
Plating Type	Unplated
UPC	781810420331

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.41 in
Dimension - Height inch	2.09 in
Dimension - Width fraction	1-5/7 in
Dimension - Width inch	1.71 in

Conductor Related

Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)