



UCT32R

by Burndy
Catalog ID: UCT32R

Aluminum Parallel Groove Clamp, Run: Cu & AL: 1 Sol. - 400, ACSR: 2 - 336.4, Tap: Cu & AL: 8 Sol. - 4/0, ACSR: 6 - 4/0 Non Prefilled PENETROX™ Connector

Product Details

General

Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	FASTAP™
UPC 12 Digit	7818106438155

Dimensions

Dimension - Height inch	2.62 in
Dimension - Length Overall inch	1.62 in
Dimension - Width inch	2.82 in

Conductor Related

Conductor - AAAC 5005 Size	6 STR - 336.4
Conductor - AAAC 5005 Size Range	6 STR - 336.4
Conductor - AAAC 6201 Size	6 STR - 336.4
Conductor - AAAC 6201 Size Range	6 STR - 336.4
Conductor - ACSR Str Size	6 STR - 336.4
Conductor - ACSR Str Size A Range	2 Str. - 336.4
Conductor - ACSR Str Size B Range	6 Str. - 4/0
Conductor - AL Str Size A	1 SOL - 400
Conductor - AL Str Size A Range	1 Sol. - 400
Conductor - AL Str Size B	8 SOL - 4/0 STR
Conductor - AL Str Size B Range	8 Sol. - 4/0 Str.
Conductor - Copper Solid Size	8-400
Conductor - Copper Solid Size Range	8-400
Conductor - Copper Str Size A Range	1 Sol. - 400
Conductor - Copper Str Size B Range	8 Sol. - 4/0 Str.

Conductor Type

- AAAC C 5005-Size
- AAAC C 6201-Size
- ACSR C Str-Size
- AL C Str-Size A
- AL C Str-Size B
- CU C Solid-Size
- CU C Str-Size A
- CU C Str-Size B
- CU Weld C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)