



## UGSKIT8

by Burndy  
Catalog ID: UGSKIT8

Direct Burial Splice Kit, 14-8 AWG, w/ Heavy Wall Heat Shrink Sleeve.

Features: Type UGS UF Splice Kit Consists Of A UF Splice Connector And A Heavy Wall Heat Shrink Sleeve, The UF Splice Connector Can Accommodate Up To Four UF Conductors And Is Installed With Common Installation Tools, The Heavy Wall Heat Shrink Sleeve Is Lined With An Adhesive Material, Providing A Watertight Splice That Can Withstand Abrasions That May Occur During Direct Burial Applications, Heat Shrink Sleeve Installed With Standard Propane Torch, Or Electric Heat Gun, Includes: (4) 1/2 IN Hex Screws

## Product Details

### General

Application	For UF Direct Burial
Connector Type	Splice;Reducer
Hex Size	1/2
Material	Aluminum
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194
Type	UGSKIT8
UPC	781810175255

### Dimensions

Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	8.00 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size	8 AWG
Conductor - AL Str Size Range	8 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	14 AWG-8 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)