



UH143

by Burndy
Catalog ID: UH143

Cast Cu Alloy Bus Support, 3/4" IPS, 3" Bolt Dia, 3/8" Bolt

Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	240 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2-13 x 1" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810004418
UPC 12 Digit	7818100044188

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - G inch	2.00 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	3/4 IPS
Conductor - Copper Tube EH Size Range	3/4 IPS
Conductor - Copper Tube Std Size	3/4 IPS
Conductor - Copper Tube Std Size Range	3/4 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)