



UH153CG9

by Burndy
Catalog ID: UH153CG9

Prop 65 Notice

Copper Bus Connectors

Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	621945049338
UPC 12 Digit	6219450493388

Dimensions

Bolt Circle Diameter	3.00 in
----------------------	---------

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	1 IPS IPS
Conductor - Copper Tube EH Size Range	1 IPS IPS
Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Copper Tube Std Size Range	1 IPS IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)