



UH155

by Burndy
Catalog ID: UH155

Prop 65 Notice

Cast Cu Alloy Bus Support, 1" IPS, 5" Bolt Dia, 3/8" Bolt

Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	240 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810004432
UPC 12 Digit	7818100044322

Dimensions

Bolt Circle Diameter	5.00 in
Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - G inch	2.25 in
Dimension - Height fraction	3-1/4 in
Dimension - Height inch	3.25 in
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Width fraction	2-7/8 in
Dimension - Width inch	2.88 in
Dimension - Width mm	73 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	1 IPS
Conductor - Copper Tube EH Size Range	1 IPS
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)