



## UH163B

by Burndy  
Catalog ID: UH163B

Prop 65 Notice

Copper Bus Connectors

## Product Details

### General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Base mounting kit (w nuts)
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2-13 x 1 1/2" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810627099
UPC 12 Digit	7818106270999

### Dimensions

Bolt Circle Diameter	3.00 in
Dimension - G inch	2.25 in
Dimension - Height inch	3.44 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width inch	3.50 in
Dimension - Width mm	89 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	1 1/4 IPS IPS
Conductor - Copper Tube EH Size Range	1 1/4 IPS IPS
Conductor - Copper Tube Std Size	1 1/4 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/4 IPS IPS

Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU Tube EH-Size</li> </ul>
Number Of Conductors	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)