



UH193B

by Burndy
Catalog ID: UH193B

Prop 65 Notice

Copper Bus Connectors

Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Base mounting kit (w nuts)
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2-13 x 1 1/2" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	78181007764
UPC 12 Digit	781810077644

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - G inch	3.13 in
Dimension - Height inch	5.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	2 1/2 IPS IPS
Conductor - Copper Tube EH Size Range	2 1/2 IPS IPS
Conductor - Copper Tube Std Size	2 1/2 IPS IPS

Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor Type	<ul style="list-style-type: none">• CU Tube Std-Size• CU Tube EH-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)