



## UH193W

by Burndy  
Catalog ID: UH193W

Prop 65 Notice

Cast Cu Alloy Bus Support-Complete Part, 2.5" IPS, 3" Bolt Dia, 1/2" Bolt

## Product Details

### General

Application	Substation
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	480 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2-13 x 1" LG
One Wrench Installation	Y
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Cable or Tube to Insulator Bus Supports
UPC	781810551318
UPC 12 Digit	7818105513188

### Dimensions

Bolt Circle Diameter	3.00 in
Dimension - B Length inch	3.00 in
Dimension - G inch	3.13 in
Dimension - Height inch	5.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	2 1/2 IPS
Conductor - Copper Tube EH Size Range	2 1/2 IPS

Conductor - Copper Tube Std Size	2 1/2 IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU Tube EH-Size</li> </ul>
Number Of Conductors	1

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)