



VG5

by Burndy
Catalog ID: VG5

Prop 65 Notice

Cu Alloy Vise Connectors, 2/0 Str - #3 Sol

Product Details

General

Connector Type	Stud Connector
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	WISEIT™
UPC	781810475157

Dimensions

Bolt Size	9/16 in
Dimension - B Length fraction	49/50 in
Dimension - B Length inch	0.94 in
Dimension - Pad Width inch	1.28 in
Dimension - Pin Diameter inch	1.80 in

Conductor Related

Conductor - Copper Solid Run	3 - 2/0
Conductor - Copper Solid Run Range	3 - 2/0
Conductor - Copper Solid Size	3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	3 AWG-2/0 AWG
Conductor - Copper Solid Tap	3 - 2/0
Conductor - Copper Solid Tap Range	3 - 2/0
Conductor - Copper Str Run	3 - 2/0
Conductor - Copper Str Run Range	3 - 2/0
Conductor - Copper Str Tap	3 - 2/0
Conductor - Copper Str Tap Range	3 - 2/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Carton Quantity	125 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)