



VT2825NK

by Burndy
Catalog ID: VT2825NK

V Style Connectors

Product Details

General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended in-lb	0.9 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Nickel
Trade Name	VARITAP™
Type	Bolted Tees
UPC	781810305850
UPC 12 Digit	7818103058500

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap
----------------	--

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)