



VT4040

by Burndy
Catalog ID: VT4040

Prop 65 Notice

High Cu Alloy VARITAP T-Connector, Bolted, Cable to Cable, 500 - 800 Kcmil(Run), 500 - 800 Kcmil(Tap)

Product Details

General

| | |
|---|------------------------|
| Application | Substation |
| Connector Type | T-Connector |
| Installation Torque Recommended Run in-lb | 500 LBS/in |
| Installation Torque Recommended Tap in-lb | 500 LBS/in |
| Installation Torque Recommended in-lb | 4.3 LBS/in |
| Material | Copper Alloy |
| Material - Hardware | DURIUM™ Silicon Bronze |
| One Wrench Installation | Y |
| Physical Attribute - Number of Run Conductors | 1 |
| Physical Attribute - Number of Tap Conductors | 1 |
| Plated | N |
| Plating Type | Unplated |
| Trade Name | VARITAP™ |
| Type | Bolted Tees |
| UPC | 781810005651 |
| UPC 12 Digit | 7818100056511 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Height fraction | 2-5/8 |
| Dimension - Height inch | 2.56 in |
| Dimension - L Length Overall mm | 114 mm |
| Dimension - Length Overall inch | 4.50 in |
| Dimension - Width fraction | 2-5/8 in |
| Dimension - Width inch | 2.63 in |
| Dimension - Width mm | 67 mm |

Electrical Ratings

| | |
|--------------|--------|
| Rating - KVA | 230 kV |
|--------------|--------|

Conductor Related

| | |
|------------------------------------|---|
| Conductor - Connection Combination | Cable to Cable |
| Conductor - Copper Str Run | 500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil |

| | |
|----------------------------------|--|
| Conductor - Copper Str Run Range | 500 kcmil-800 kcmil |
| Conductor - Copper Str Tap | 500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil |
| Conductor - Copper Str Tap Range | 500 kcmil-800 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)